

COMPRESSION ADAPTOR

(COMP-0036-ABS-R25 - 25mm)

Compatible[®]

EN

This component is used where there is the requirement to reduce from 25mm pipe to a 10mm nylon tube to sample through a range of sampling heads. The 10mm tubing simply push fits and clicks into position, and can be released by pushing on the blue ring.

Installation Instructions:

Use the correct solvent Plusbond 3019. Do not paint. Keep pipe clean and free from dust. Do not install in direct sunlight. Only install with approved pipe. Do not use solvents to clean, only soapy water.

TR

Bu bileşen, bir dizi numune alma başlığı aracılığıyla numune almak için 25 mm borudan 10 mm naylon tüpe indirgeme gereksinimi olduğunda kullanılır. 10 mm'lik boru basitçe itilerek ve tıklanarak yerine oturur ve mavi halka itilerek serbest bırakılabilir.

Kurulum Talimatları:

Doğru solvent Plusbond 3019 kullanın. Boya yapmayın. Boruyu temiz ve tozsuz tutun. Doğrudan güneş ışığı altında montaj yapmayın. Sadece onaylı boru ile monte edin. Temizlemek için solvent kullanmayın, sadece sabunlu su kullanın.

PART NO.:
COMP-0036-ABS-R25

PIPE COLOUR:
Red

OPERATING TEMP.:
- 40 c to 70 c'

WEIGHT:
23.2g

FITTINGS COLOUR:
Red

DIAMETER TOLERANCE:
+ / - 0.15mm'

WALL THICKNESS:
2mm

