

# FLUSH KIT WITH T COMPRESSION ADAPTER (COMP-0042F-ABS-R25 - 25mm)

Compatible®

## EN

The adapter is used to join the 10mm tubing to the body of the T piece, simply push the tube into the adapter until it clicks in position. It can be removed by pushing on the black circular ring.

### Installation Instructions:

Use the correct solvent Plusbond 3019. Do not paint. Keep pipe clean and free from dust. Do not install in direct sunlight. Only install with approved pipe. Do not use solvents to clean, only soapy water.

## TR

Adaptör, 10 mm'lik boruyu T parçasının gövdesine bağlamak için kullanılır, boruyu yerine oturana kadar adaptörün içine itmeniz yeterlidir. Siyah dairesel halka üzerine bastırarak çıkarılabilir.

### Kurulum Talimatları:

Doğru solvent Plusbond 3019 kullanın. Boya yapmayın. Boruyu temiz ve tozsuz tutun. Doğrudan güneş ışığı altında montaj yapmayın. Sadece onaylı boru ile monte edin. Temizlemek için solvent kullanmayın, sadece sabunlu su kullanın.

**PART NO.:**  
COMP-0042F-ABS-R25

**PIPE COLOUR:**  
Red

**OPERATING TEMP:**  
- 40 c to 70 c'

**WEIGHT:**  
113.8 g

**FITTINGS COLOUR:**  
Red

**DIAMETER  
TOLERANCE:**  
+ / - 0.15mm'

**WALL THICKNESS:**  
2mm

